

LED Driver with ZigBee Solution

 ZigBee wireless control technology



Mesh network nodes support

Driver Selection

MEAN WELL ELG / LCM / NPF / PWM ZB series





Multi-channel LED Dimmer with EnOcean Solution

- EnOcean wireless control technology
- Easy installation and configuration
- 6 protected and
- independent dimming output channels • Up to 128 wireless batteryless switches
- Suitable for constant voltage lighting application
- Up to 30 meter wireless distances

Selection

MEAN WELL LED drivers with C.V. mode



### Wi Fi

#### **Wireless Smart Home Controller**

- · RF/WiFi/IR Remote control
- Free iOS /Android APP download and big data accessibility
- Smart scenes for Home Automation and Lighting Control Systems
- Easy installation and configuration
- · Energy saving and monitoring

Driver

MEAN WELL LED Driver with Selection 3-in-1 dimming function





· Easy installation and configuration

Easy lighting group

Solution

DALI interface

**PLCM-25/40/60DA** 

**LED Driver with DALI** 

with DAP-04

Driver Selection

ELG / LCM / NPF / PWM with DA series

### PELG-150-C1400PLC

**LED Driver with PLC Solution** 

- Power line carrier technology
- Dimming control via power line communication

Driver Selection

MEAN WELL ELG with PLC series



Easy installation and configuration





Multi-functional LED Dimmer & **LED Controller** 

- RF wireless remote control
- Adjustable brightness / color temperature / RGBW
- Suitable for LED strips application

Driver Selection

MEAN WELL LED drivers with C.V. mode



**AC plug-in LED Module** 

- AC mains direct driving
- Systematic efficacy >100 lm/w @3000K
- CRI>80: Power Factor > 0.95
- T.H.D. < 20%
- Easy installation and configuration

Driver Selection


Other MEAN WELL LED drivers available



- · Constant current & constant voltage output
- · Suitable for outdoor LED lighting

Driver Selection

HLG 40~600H series ELG 75~240 series



NCL-CL1-01 IRL-CL2-01 IRL-RGB-01

**LED Strips** 

- 12V LED Strips
- Uniform brightness, high stability
- · Tailored length per application demand

Driver Selection

MEAN WELL switching power supply with 12Vdc



PIR (Passive Infrared) Dimming Sensor

- Built-in Passive Infrared sensor module
- MCU controller, no relay contact
- Adjustable off-time dealy / dimming level / sensitivity

Driver Selection

MEAN WELL LED Driver with 3-in-1 dimming or 12Vdc auxiliary



# Your Reliable Power Pariner



### info@meanwell.com

www.meanwell.com





## Driving Your Life Intelligently

#### China

Taiwan (Headquarters)

New Taipei City, Taiwan, 24891 **Tel** +886-2-2299-6100(rep.) Fax +886-2-2299-6200(rep.) +886-2-2298-0818(sales) e-mail info@meanwell.com Web www.meanwell.com

MEAN WELL ENTERPRISES CO., LTD. No. 28, Wuquan 3rd Road, Wugu District,

#### MEAN WELL (GUANGZHOU) ELECTRONICS CO., LTD.

2F, A Building, Yuean Industry Park, Huangcun, Dongpu Town, Tianhe District, Guangzhou, China

**Tel** +86-20-2887-1200 +86-755-2359-1630 (Shenzhen Office) Fax +86-20-8201-0507 +86-20-8201-0507 (Shenzhen Office)

 $\textbf{e-mail} \hspace{0.2cm} \textbf{info@meanwell.com.cn} \hspace{0.2cm} \textbf{Web} \hspace{0.2cm} \textbf{www.meanwell.com.cn}$ 

#### SUZHOU MEAN WELL TECHNOLOGY CO., LTD.

No.77, Jian-Ming Rd. Dong-Qiao, Pan-Yang Ind. Park, Huang-Dai Town, Xiang-Cheng District, Suzhou, Jiang-Su, China

**Tel** +86-512-6508-8600 Fax +86-512-6508-8700 e-mail info@meanwell.cc Web www.meanwell.cc

#### U.S.A.

#### MEAN WELL USA, INC.

44030 Fremont Blvd., Fremont, CA 94538, U.S.A. Fax +1-510-683-8899 e-mail info@meanwellusa.com Web www.meanwellusa.com

#### Europe

#### MEAN WELL EUROPE B.V.

Langs de Werf 8, 1185XT Amstelveen, the Netherlands **Tel** +31-20-758-6000 Fax +31-20-758-6001 e-mail info@meanwell.eu Web www.meanwell.eu



