



## **Declaration of RoHS & PFOS Conformity**

To minimize the environmental impact and take more responsibility to the earth we live, MEAN WELL hereby confirms that the following product series comply with Directive of the European Parliament 2011/65/EU、2015/863/EU - ROHS (Restriction of Hazardous Substances) and 2006/122/EC - PFOS (PerFluoroOctane Sulfonates)

### **Content of Compliance**

Lead (Pb)	<0.1 % by weight (1000 ppm)
Mercury (Hg)	<0.1 % by weight (1000 ppm)
Cadmium (Cd)	<0.01 % by weight (100 ppm)
Hexavalent Chrome (Cr <sup>6+</sup> )	<0.1 % by weight (1000 ppm)
Polybrominated Biphenyls (PBBs)	<0.1 % by weight (1000 ppm)
Polybrominated Diphenyl Ethers (PBDEs)	<0.1 % by weight (1000 ppm)
Bis(2-ethylhexyl) phthalate (DEHP)	<0.1 % by weight (1000 ppm)
Butyl benzyl phthalate (BBP)	<0.1 % by weight (1000 ppm)
Dibutyl phthalate (DBP)	<0.1 % by weight (1000 ppm)
Diisobutyl phthalate (DIBP)	<0.1 % by weight (1000 ppm)
Decabromobiphenyl(DecaBDE )	n.d. (Not Detected)
PFOS	<0.1 % by weight (1000 ppm)

### **Product Series**

Please refer to the attached list for details.

### **Delivery**

Products announced to be RoHS and PFOS compliance can be provided now. Please contact our sales representatives for details.

Jerry Lin / President  
MEAN WELL Enterprises Co., Ltd

Product Family	Series
<b>G3</b>	RS-15/25/35/50/75/100/150, RD-35/50/65/85/125, RID-50/65/85/125, RT-50/65/85/125, RQ-50/65/85/125
<b>G2/SE/LRS</b>	S-25/40/60/100F/150/210/250/320, T-40, D/ID/T/IT/Q/IQ-60, D/T/Q-120, SC-150, SE-100/200/350/450/600/1000/1500,LRS-35/50/75/100/150/150F/200/350
<b>LED Sign Panel</b>	ERP-350, HSN-200/300, NEL-200/300/400, HSP-150/200/250/300, HDP-190/240, ERPF-400, UHP-200A/200(R)/350(R)/ 500(R),LHP-200
<b>PFC</b>	SP-75/100/150/200/240/320/480/500/750, USP-150/225/350/500, TP-75/100/150, QP-100/150/200/320/375, PSP-500/600, PSPA-1000, RSP-75/100/150/200/320/500/750/1000/1500/1600/2000/2400/3000, RST-5000/10000, SPV-150/300/1500, HRP-75/100, HRP(G)-150/200/300/450/600, HRPG-1000, MSP-100/200/300/450/600/1000, HEP-100/150/185/240/320/480/600, DPU-3200
<b>LED</b>	HLG-40H/60H/80H/100H/120H/150H/185H/240H/320H/480H-(C), HLG-600H, CLG-60/100/150, POB, RFP, NCL, HSG-70, FDL-65, CEN-60/75/100, DLP-04, HVG(C)-65/100/150/240/320/480/650, ELG-75/100/150/200/240, ELG-75/100/150/200/240-C, ELGT-150-C, ELGC-300, LDV-185, FDLC-80/100, GSC18/25/40, SDP-001, IRL, OWA-60/90/120, HBG-60(P)/100(P)/160(P)/200/240(P), HBGC-300, ULP-150, APV-8(E)/12(E)/16(E)/25/35, NPF-40(D)/60(D)/90(D)/120(D), HLN-40H/60H/80H, LDB, PLN-20/30/45/60/100, PLC-30/45/60/100, PLM-12(E)/25(E)/40(E), PCD-16/25/40/60, IDLV-25/45/65, DAP-04(S01), SPD-20(HP), LDH-45(DA), LDD-DA, IDLC-25/45/65, IDPV-25/45/65, IDPC-25/45/65, ODLC-45/65, LDD-L/H, ELN-30/60 ODLV-45/65, PLD-16/25/40/60, LPH(C)-18, LCM-25(DA)/40(DA)/40U(DA)/60(DA)/60U(DA), APC-8(E)/12(E)/16(E)/25/35, LPVL-150, LDC-35/55/80(DA), LCM-40/60(U)EO, PWM-40/60/90/120, HLP-40H/60H/80H, LPF-16(D)/25(D)/40(D)/60(D)/90(D), LPFH-60(D), PLP-20/30/45/60, LPL(C)-18, LPV(C)-20/35/60/100/150,
<b>DIN</b>	DRA-40/60, MDR-10/20/40/60/100, DR-15/30/45/60/75/100/120, DRH-120, DRP-240/480/480S, DRT-240/480/960, HDR-15/30/60/100/150, DR-UPS40, EDR-75/120/150, NDR-75/120/240/480, SDR-75/120/240/480(P)/960, WDR-120/240/480, TDR-240/480/960, DR-RDN20, KNX-20E-640, KDA-64, KSI-01U, KSR-01IP, KSC-01L
<b>Modular</b>	MP450/650/1K0, MS-75/150/210/300/360, MD-100, NMP650/1K2, NMS-240
<b>19' Rack Power</b>	RCP-1000/1600/2000, RCP-1U, RKP-1U, RHP-1U, RCP-MU, RKP-CMU1, RKP-1U-CMU1, DRP-3200, DHP-1UT
<b>Open Frame</b>	NFM-05/10/15/20, MFM-05/10/15/20/30, PM-05/10/15/20, PS-05/15, MPM-05/10/15/20/30/30ST, PS/PD-25, PS-35, PS/PD/PT-45/65, RPD/RPT-65, PD-110, PQ-100, PPQ-100, PPS-125/200, PPT-125, LPS-50/75/100, LPP-100/150, ASP-150, PID-250, ELP-75, MPS/MPD/MPT/MPQ-120/200, RPT-160-C, RPS-120/200/300(-C), RPS-400/500(-C/-TF/-SF), IRM-01(S)/02(S)/03(S)/05/10/15/20/30(ST)/45(ST)/60(ST), RPS/RPD/RPT-65/75, RPS/RPD/RPT-60, EPS-15/25/35/45S/45(C)/65S/65(C)/120, EPP-100/150/200/300/400/500, MPS-30, MPS/MPD/MPT-45/65, RPS-30/45/65, RPS(G)/RPD(G)/RPT(G)-160
<b>Charger</b>	GC30/120/160/220/330, PA/PB/PS-120, ESC/ESP-120/240, PB-230/300/360/600/1000, HEP-600C, RPB-1600, RCB-1600, ENP/ENC-120/180/240/360, DBU-3200, DBR-3200, DHB-1UT
<b>Adaptor</b>	GS05/06/12/15/18/25/36/40/60/90/120/160/220/280, GE12/18/24/30, ES18/25, P25/50, GP25/50, MES-30/50, GEM12I/18I/30I/40I/60I, GSM06/18/25/36/40/60/90/120/160/220, GST18/25/36/40/60/90/120/160/220/280, SGA12/18/25/40/60
<b>Security</b>	SCP-35/50/75, ADS-55/155, AD-55/155, ADD-55/155, PSC-35(C)/60(C)/100(C)/160(C), DRC-40/60/100
<b>ATX / Gaming Power</b>	YP-350J, YP-350A/400A/450A, IPC-200/250/300, MWP-610(P)
<b>DC/DC Converter</b>	SD-15/25/50/100/150/200/350/500/1000, RSD-30/60/100/150/200/300, SDM30, NSD, NID, PSD, SBT, SFT, DET, SRS, SUS, SPR, SMU, SMA, SPU, SPA, SPB, SCW, SLW, SKE, SKA, SKM, DCW, DLW, DKE, DKA, TKA, MHB, ,DPU, SPAN, DPAN, SPBW, DPBW, SLC, DLC, SCWN, DCWN, DKM, SKMW, DKMW, MDS, MDD, SBTN, SFTN, DETN, ,DDR-15/30/60/120/240, RSDW/RDDW08/10/20
<b>Inverter</b>	TS-200/400/700/1000/1500/3000, TN-1500/3000, A301/A302, IRC1/2/3, ISI-500/501, GSI-3000/4600/5000
<b>Power Cord</b>	YP** + YC**
<b>Accessories</b>	DRL, DRP, MHS, TBC, FAP, FAS

**\*\* For other products not listed above, please contact our sales representatives for availability**

2018.07.01 updated