

DC-DC转换器快选表



DC-DC
模块型快选表

应用	封装	系列		功率	输入电压	输出电压	输出稳压	隔离电压	工作温度	尺寸 (长 x 宽 x 高 mm)	安规
		图片	型号								
医疗产业	SIP		MDS01-N	1W	5V(4.5~5.5V) 12V(10.8~13.2V) 24V(21.6~26.4V)	3.3V 5V 12V 15V	无稳压	6KVDC	-40~+95°C	19.7 x 7.1 x 11.5	 UL/EAC/ CE/CB/ UKCA
			MDD01-N			±5V ±12V ±15V					
			MDS02-N	2W	5V(4.5~5.5V) 12V(10.8~13.2V) 24V(21.6~26.4V)	3.3V 5V 12V 15V					
			MDD02-N			±5V ±12V ±15V					
	DIP24		MDS03	3W	12V, 48V(9~36V) 24V, 48V(18~75V)	5V 12V 15V	稳压	6KVDC/ 4.2KVAC	-40~+90°C	31.8 x 20.3 x 12.2	 EAC/CE/ UKCA
			MDD03			±5V ±12V ±15V					
			MDS06	6W	12V, 24V(9~36V) 24V, 28V(18~75V)	5V 12V 15V					
			MDD06			±5V ±12V ±15V					
	2"x1"		MDS15	15W	12V(9~18V) 24V(18~36V) 48V(36~75V)	5V 12V 15V 24V	4KVAC	-40~+90°C	50.8 x 25.4 x 12		
			MDS20	20W	12V(9~18V) 24V(18~36V) 48V(36~75V)	5V 12V 15V 24V					4KVAC