

# DC-DC转换器快选表



DC-DC  
模块型快选表

应用	封装	系列		功率	输入电压	输出电压	输出稳压	隔离电压	工作温度	尺寸 (长 x 宽 x 高 mm)	安规	
		图片	型号									
光伏储能产业	DIP		DDRH-15-P	15W	150~1500V	5V 12V 15V 24V	稳压	4KVAC	-40~+80°C	76.2 x 50.8 x 25	 EAC/CE/ UKCA	
			DDRH-30-P	30W	150~1500V	12V 15V 24V 48V						
			DDRH-45-P	45W	150~1500V	12V 15V 24V 48V						
			DDRH-15-ST	15W	150~1500V	5V 12V 15V 24V						
			DDRH-30-ST	30W	150~1500V	12V 15V 24V 48V						
			DDRH-45-ST	45W	150~1500V	12V 15V 24V 48V						
			DDRH-15-DR	15W	150~1500V	5V 12V 15V 24V						
			DDRH-30-DR	30W	150~1500V	12V 15V 24V 48V						
			DDRH-45-DR	45W	150~1500V	12V 15V 24V 48V						
	----		DDRH-60	60W	150~1500V	5V 12V 24V 48V	----	4KVAC	-30~+80°C	57 x 93.5 x 105		 CSA/EAC/ CE/UKCA
	----		DDRH-120	120W	250~1500V	12V 24V 32V 48V	----	4KVAC	-40~+80°C	63 x 125.2 x 115		 CSA/ DEKRA/ EAC/CB/ CE/UKCA
	----		DDRH-240	240W	250~1500V	12V 24V 32V 48V	----	4KVAC	-40~+80°C	85.5 x 125.2 x 129.2		
	----		RSDH-150	150W	250~1500V	12V 24V 32V 48V	----	4KVAC	-40~+80°C	191 x 86 x 41		 CSA/ DEKRA/ EAC/CB/ CE/UKCA
	----		RSDH-300	300W	250~1500V	12V 24V 32V 48V	----	4KVAC	-40~+80°C	237 x 86 x 41		