



Declaration of RoHS & PFOS Conformity

To minimize the environmental impact and take more responsibility to the earth we live, MEAN WELL hereby confirms that the following product series comply with Directive of the European Parliament 2011/65/EU - ROHS (Restriction of Hazardous Substances) and 2006/122/EC - PFOS (PerFluoroOctane Sulfonates)

Content of Compliance

Lead	<0.1 % by weight (1000 ppm)
Mercury	<0.1 % by weight (1000 ppm)
Cadmium	<0.01 % by weight (100 ppm)
Hexavalent Chrome(Cr ⁺⁶)	<0.1 % by weight (1000 ppm)
PBBs	<0.1 % by weight (1000 ppm)
PBDEs	<0.1 % by weight (1000 ppm)
Decabromobiphenyl(DecaBDE)	n.d. (Not Detected)
PFOS	<0.1 % by weight (1000 ppm)

Product Series

Please refer to the attached list for details.

Delivery

Products announced to be RoHS and PFOS compliance can be provided now. Please contact our sales representatives for details.

Jerry Lin / President
MEAN WELL Enterprises Co., Ltd.

Product Family	Series
G3	RS-15/25/35/50/75/100/150, RD-35/50/65/85/125, RID-50/65/85/125, RT-50/65/85/125, RQ-50/65/85/125
G2/SE/LRS	S-25/40/60/100F/150/210/250/320, T-40, D/ID/T/IT/Q/IQ-60, D/T/Q-120, SC-150, SE-100/200/350/450/600/1000/1500, LRS-35/50/75/100/150/150F/200/350
LED Sign Panel	ERP-350, HSN-200/300, NEL-200/300/400, HSP-150/200/250/300, HDP-190/240, ERPF-400, UHP-200
PFC	SP-75/100/150/200/240/320/480/500/750, USP-150/225/350/500, TP-75/100/150, QP-100/150/200/320/375, PSP-500/600, RSP-75/100/150/200/320/500/750/1000/1500/1600/2000/2400/3000, RST-5000/10000, SPV-150/300/1500, HRP-75/100, HRP(G)-150/200/300/450/600, MSP-100/200/300/450/600, HEP-100/150/185/240/320/600
LED	HLG-40H/60H/80H/100H/120H/150H/185H/240H/320H/480H/600H, HLG-60H/80H/120H/185H/240H/320H/480H/-C, HVG(C) -65/100/150/240/320/480, CLG-60/100/150, ELG-75/100/150/200/240, ELG-75/100/150/200/240-C, HSG-70, FDL-65, CEN-60/75/100, HBG-60(P)/100(P)/160(P)/240(P), ULP-150, LDV-185, HLN-40H/60H/80H, PLN-20/30/45/60/100, PLC-30/45/60/100, PLM-12(E)/25(E)/40(E), PCD-16/25/40/60, IDLV-25/45/65(A), IDLC-25/45/65(A), IDPV-45/65(A), IDPC-45/65(A), ODLC-45/65(A), PLD-16/25/40/60, GSC18/25/40, OWA-60/90/120, LCM-25(DA)/40(DA)/40U(DA)/60(DA)/60U(DA), LPF-16(D)/25(D)/40(D)/60(D)/90(D), LPFH-60(D), NPF-40(D)/60(D)/90(D)/120(D), PWM-40/60/90/120, HLP-40H/60H/80H, PLP-20/30/45/60, ELN-30/60, LPH(C)-18, LPL(C)-18, LPV(C)-20/35/60/100/150, LPVL-150, APV-8(E)/12(E)/16(E)/25/35, APC-8(E)/12(E)/16(E)/25/35, LDD-L/H, LDB, LDH-45(DA), DAP-04(S01), SPD-20, SDP-001, POB, RFP, NCL, IRL
DIN	DRA-40/60, MDR-10/20/40/60/100, DR-15/30/45/60/75/100/120, DRH-120, DRP-240/480/480S, DRT-240/480/960, HDR-15/30/60, EDR-75/120/150, NDR-75/120/240/480, SDR-75/120/240/480(P)/960, WDR-120/240/480, TDR-480/960, DR-RDN20, DR-UPS40, KNX-20E-640
Modular	MP450/650/1K0, MS-75/150/210/300/360, MD-100
19' Rack Power	RCP-1000/1600/2000, RCP-1U, RKP-1U, RHP-1U, RCP-MU, RKP-CMU1, RKP-1U-CMU1
Open Frame	NFM-05/10/15/20, PM-05/10/15/20, PS-05/15, PS/PD-25, PS-35, PS/PD/PT-45, PS/PD/PT-65, RPD/RPT-65, PD-110, PQ-100, PPQ-100, PPS/PPT-125, LPS-50/75/100, LPP-100/150, ASP-150, PPS-200, PID-250, ELP-75, IRM-01(S)/02(S)/03(S)/05/10/15/20/30(ST)/45(ST)/60(ST), EPS-15/25/35/45S/45(C)/65S/65(C)/120, EPP-100/150/200/300/400, MPS-30, MPS/MPD/MPT-45, RPS-30/45/65, RPS/RPD/RPT-60, MPS/MPD/MPT-65, RPS/RPD/RPT-75, RPS(G)/RPD(G)/RPT(G)-160, MPS/MPD/MPT/MPQ-120, MPS/MPD/MPT/MPQ-200, RPS-120(-C)/-200(-C)/-300(-C)/-400(-C/-TF/-SF)
Charger	GC30/120/160/220/330, PA/PB/PS-120, ESC/ESP-120, ESC/ESP-240, PB-230/300/360/600/1000, HEP-600C, RPB-1600, RCB-1600, ENP/ENC-120/180
Adaptor	GS05/06/12/15/18/25/36/40/60/90/120/160/220/280, GE12/18/24/30, ES18/25, P25/50, GP25/50, MES-30/50, GEM12I/18I/30I/ 40I GSM06/18/25/36/40/60/90/120/160/220, GST18/25/36/40/60/90/120/160/220/280, SGA12/18/25/40/60
Security	SCP-35/50/75, ADS-55/155, AD-55/155, ADD-55/155, PSC-35(C)/60(C)/100(C)/160(C), DRC-40/60/100
ATX / Gaming Power	YP-350J, YP-350A/400A/450A, IPC-200/250/300, MWP-610(P)
DC/DC Converter	SD-15/25/50/100/150/200/350/500/1000, RSD-100/150/200/300, SDM30, NSD,NID, PSD, SBT, SFT, DET, SRS, SUS, SPR, SMU, SMA, SPU, SPA, SPB, SCW, SLW, SKE, SKA, SKM, DCW, DLW, DKE, DKA, TKA, MHB
Inverter	TS-200/400/700/1000/1500/3000, TN-1500/3000, A301/A302, IRC1/2/3, ISI-500/501, GSI-3000/4600/5000
Power Cord	YP** + YC**
Accessories	DRL, DRP, MHS, TBC, FAP, FAS

**** For other products not listed above, please contact our sales representatives for availability**

2016.10 update

ISO-9001 CERTIFIED

Your Reliable Power Partner