



Product Upgrade Notice:

LRS, RSP, HDR, KNX-20E series OVC III Upgrade

MEAN WELL industrial control power supplies possess a high reputation in the global market. To enhance the competitiveness of power supply products and expand the application aspects, Over Voltage Category (OVC) safety regulations for LRS-35/50/75/100/150/150F, RSP-75/100/150, HDR-15/30/60/100, KNX-20E series are upgraded from OVC II to OVC III. For further OVC III introduction, please refer to MEAN WELL 35th E-newsletter [Power supply for Overvoltage Category\(OVC\) III applications.](#)

For the revision this time, electrical specifications and safety regulations will not be influenced. Shall there be any questions, please refer to the updated specification on website or contact MEAN WELL sales representatives.

Before	<table border="1"> <tr> <td rowspan="5">ENVIRONMENT</td> <td>WORKING TEMP.</td> <td>-30 ~ +70°C (Refer to "Derating Curve")</td> </tr> <tr> <td>WORKING HUMIDITY</td> <td>20 ~ 90% RH non-condensing</td> </tr> <tr> <td>STORAGE TEMP., HUMIDITY</td> <td>-40 ~ +85°C, 10 ~ 95% RH</td> </tr> <tr> <td>TEMP. COEFFICIENT</td> <td>±0.03%/°C (0 ~ 50°C)</td> </tr> <tr> <td>VIBRATION</td> <td>10 ~ 500Hz, 5G 10min./1cycle, 60min. each along X, Y, Z axes</td> </tr> <tr> <td rowspan="5">SAFETY & EMC (Note 7)</td> <td>SAFETY STANDARDS</td> <td>UL60950-1, TUV EN60950-1, EN60335-1, EN61558-1/-2-16, CCC GB4943 approved</td> </tr> <tr> <td>WITHSTAND VOLTAGE</td> <td>I/P-O/P:3.75KVAC I/P-FG:2KVAC O/P-FG:1.25KVAC</td> </tr> <tr> <td>ISOLATION RESISTANCE</td> <td>I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH</td> </tr> <tr> <td>EMC EMISSION</td> <td>Compliance to EN55022 (CISPR22), GB9254 Class B, EN55014, EN61000-3-2Class A(≤75% Load), EN61000-3-3</td> </tr> <tr> <td>EMC IMMUNITY</td> <td>Compliance to EN61000-4-2,3,4,5,6,8,11, EN61000-6-2 (EN50082-2), heavy industry level, criteria A</td> </tr> </table>	ENVIRONMENT	WORKING TEMP.	-30 ~ +70°C (Refer to "Derating Curve")	WORKING HUMIDITY	20 ~ 90% RH non-condensing	STORAGE TEMP., HUMIDITY	-40 ~ +85°C, 10 ~ 95% RH	TEMP. COEFFICIENT	±0.03%/°C (0 ~ 50°C)	VIBRATION	10 ~ 500Hz, 5G 10min./1cycle, 60min. each along X, Y, Z axes	SAFETY & EMC (Note 7)	SAFETY STANDARDS	UL60950-1, TUV EN60950-1, EN60335-1, EN61558-1/-2-16, CCC GB4943 approved	WITHSTAND VOLTAGE	I/P-O/P:3.75KVAC I/P-FG:2KVAC O/P-FG:1.25KVAC	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH	EMC EMISSION	Compliance to EN55022 (CISPR22), GB9254 Class B, EN55014, EN61000-3-2Class A(≤75% Load), EN61000-3-3	EMC IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11, EN61000-6-2 (EN50082-2), heavy industry level, criteria A		
ENVIRONMENT	WORKING TEMP.		-30 ~ +70°C (Refer to "Derating Curve")																						
	WORKING HUMIDITY		20 ~ 90% RH non-condensing																						
	STORAGE TEMP., HUMIDITY		-40 ~ +85°C, 10 ~ 95% RH																						
	TEMP. COEFFICIENT		±0.03%/°C (0 ~ 50°C)																						
	VIBRATION	10 ~ 500Hz, 5G 10min./1cycle, 60min. each along X, Y, Z axes																							
SAFETY & EMC (Note 7)	SAFETY STANDARDS	UL60950-1, TUV EN60950-1, EN60335-1, EN61558-1/-2-16, CCC GB4943 approved																							
	WITHSTAND VOLTAGE	I/P-O/P:3.75KVAC I/P-FG:2KVAC O/P-FG:1.25KVAC																							
	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH																							
	EMC EMISSION	Compliance to EN55022 (CISPR22), GB9254 Class B, EN55014, EN61000-3-2Class A(≤75% Load), EN61000-3-3																							
	EMC IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11, EN61000-6-2 (EN50082-2), heavy industry level, criteria A																							
After	<table border="1"> <tr> <td rowspan="5">ENVIRONMENT</td> <td>WORKING TEMP.</td> <td>-30 ~ +70°C (Refer to "Derating Curve")</td> </tr> <tr> <td>WORKING HUMIDITY</td> <td>20 ~ 90% RH non-condensing</td> </tr> <tr> <td>STORAGE TEMP., HUMIDITY</td> <td>-40 ~ +85°C, 10 ~ 95% RH non-condensing</td> </tr> <tr> <td>TEMP. COEFFICIENT</td> <td>±0.03%/°C (0 ~ 50°C)</td> </tr> <tr> <td>VIBRATION</td> <td>10 ~ 500Hz, 5G 10min./1cycle, 60min. each along X, Y, Z axes</td> </tr> <tr> <td rowspan="5">SAFETY & EMC (Note 7)</td> <td>OVER VOLTAGE CATEGORY</td> <td>III ; Compliance to EN61558, EN50178, EN60664-1, EN62477-1; altitude up to 2000 meters</td> </tr> <tr> <td>SAFETY STANDARDS</td> <td>UL60950-1, TUV EN60950-1, EN60335-1, EN61558-1/-2-16, CCC GB4943.1, BSMI CNS14336-1, EAC TP TC 004, AS/NZS 60950.1(by CB) approved</td> </tr> <tr> <td>WITHSTAND VOLTAGE</td> <td>I/P-O/P:4KVAC I/P-FG:2KVAC O/P-FG:1.25KVAC</td> </tr> <tr> <td>ISOLATION RESISTANCE</td> <td>I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH</td> </tr> <tr> <td>EMC EMISSION</td> <td>Compliance to EN55032 (CISPR32) Class B, EN55014, EN61000-3-2,-3, GB/T 9254, BSMI CNS14338, EAC TP TC 020</td> </tr> <tr> <td>EMC IMMUNITY</td> <td>Compliance to EN61000-4-2,3,4,5,6,8,11, EN61000-6-2 (EN50082-2), heavy industry level, criteria A, EAC TP TC 020</td> </tr> </table>	ENVIRONMENT	WORKING TEMP.	-30 ~ +70°C (Refer to "Derating Curve")	WORKING HUMIDITY	20 ~ 90% RH non-condensing	STORAGE TEMP., HUMIDITY	-40 ~ +85°C, 10 ~ 95% RH non-condensing	TEMP. COEFFICIENT	±0.03%/°C (0 ~ 50°C)	VIBRATION	10 ~ 500Hz, 5G 10min./1cycle, 60min. each along X, Y, Z axes	SAFETY & EMC (Note 7)	OVER VOLTAGE CATEGORY	III ; Compliance to EN61558, EN50178, EN60664-1, EN62477-1; altitude up to 2000 meters	SAFETY STANDARDS	UL60950-1, TUV EN60950-1, EN60335-1, EN61558-1/-2-16, CCC GB4943.1, BSMI CNS14336-1, EAC TP TC 004, AS/NZS 60950.1(by CB) approved	WITHSTAND VOLTAGE	I/P-O/P:4KVAC I/P-FG:2KVAC O/P-FG:1.25KVAC	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH	EMC EMISSION	Compliance to EN55032 (CISPR32) Class B, EN55014, EN61000-3-2,-3, GB/T 9254, BSMI CNS14338, EAC TP TC 020	EMC IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11, EN61000-6-2 (EN50082-2), heavy industry level, criteria A, EAC TP TC 020
ENVIRONMENT	WORKING TEMP.		-30 ~ +70°C (Refer to "Derating Curve")																						
	WORKING HUMIDITY		20 ~ 90% RH non-condensing																						
	STORAGE TEMP., HUMIDITY		-40 ~ +85°C, 10 ~ 95% RH non-condensing																						
	TEMP. COEFFICIENT		±0.03%/°C (0 ~ 50°C)																						
	VIBRATION	10 ~ 500Hz, 5G 10min./1cycle, 60min. each along X, Y, Z axes																							
SAFETY & EMC (Note 7)	OVER VOLTAGE CATEGORY	III ; Compliance to EN61558, EN50178, EN60664-1, EN62477-1; altitude up to 2000 meters																							
	SAFETY STANDARDS	UL60950-1, TUV EN60950-1, EN60335-1, EN61558-1/-2-16, CCC GB4943.1, BSMI CNS14336-1, EAC TP TC 004, AS/NZS 60950.1(by CB) approved																							
	WITHSTAND VOLTAGE	I/P-O/P:4KVAC I/P-FG:2KVAC O/P-FG:1.25KVAC																							
	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH																							
	EMC EMISSION	Compliance to EN55032 (CISPR32) Class B, EN55014, EN61000-3-2,-3, GB/T 9254, BSMI CNS14338, EAC TP TC 020																							
EMC IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11, EN61000-6-2 (EN50082-2), heavy industry level, criteria A, EAC TP TC 020																								

MEAN WELL ENTERPRISES CO., LTD

Marketing Department