



















■ Features

- Universal AC input / Full range(up to 305VAC)
- · Built-in active PFC function
- High efficiency up to 93.5%
- · Fanless design, cooling by free air convection
- -55~+70°C wide operating range
- · Aluminum case and filling with heat-conducted silicone
- · IP65 design, optional IP68 rated model available
- Meet 6KV surge immunity level
- · Withstand 10G vibration test
- · Operating altitude up to 5000 meters (Note.8)
- Protections: Short circuit / Overload / Over voltage / Over temperature
- 6 years warranty (Note.10)


Applications

- Outdoor telecommunication equipment
- · Outdoor electronic signage and billboard
- · Petroleum plant or mine shaft facility

Description

HEP-240 is a 240W industrial AC/DC power supply featuring the outstanding capability to operate under a harsh environment with high dust density, humidity, vibration and altitude. The entire series is housed with a robust aluminum case and fully potted with heat-conducted silicone. Thanks to state-of-the-art design, the working efficiency is up to 93.5%, enabling HEP-240, with a fanless design, perfectly work between -55°C and +70°C under free air convection.

■ Model Encoding



A: Standard model, IP65, Vo and Io level can be adjusted through internal potentiometer.


Blank: Optional model, IP68, with fixed Vo and Io level.



SPECIFICATION

MODEL			HEP-240-12	HEP-240-15	HEP-240-24	HEP-240-36	HEP-240-48	HEP-240-54
ОИТРИТ	DC VOLTAGE		12V	15V	24V	36V	48V	54V
	RATED CURRENT		16A	15A	10A	6.7A	5A	4.45A
	RATED POWER		192W	225W	240W	241.2W	240W	240.3W
	RIPPLE & NOISE (max.) Note.2		150mVp-p	150mVp-p	150mVp-p	250mVp-p	250mVp-p	350mVp-p
	VOLTAGE ADJ. RANGE Note.5		11.2 ~ 12.8V	14 ~ 16V	22.4 ~ 25.6V	33.5 ~ 38.5V	44.8 ~ 51.2V	50 ~ 57V
	CURRENT ADJ. RANGE		Can be adjusted by internal potentiometer for A type only					
			8 ~ 16A	7.5 ~ 15A	5 ~ 10A	3.3 ~ 6.7A	2.5 ~ 5A	2.23 ~ 4.45A
	VOLTAGE TOLERANCE Note.3		±2.5%	±2.0%	±1.0%	±1.0%	±1.0%	±1.0%
	LINE REGULATION		±0.5%	±0.5%	±0.5%	±0.5%	±0.5%	±0.5%
	LOAD REGULATION		±2.0%	±1.5%	±0.5%	±0.5%	±0.5%	±0.5%
	SETUP, RISE TIME Note.6		1000ms,80ms/115VAC 500ms,80ms/230VAC at full load					
	HOLD UP TIME (Typ.)		15ms at full load 230VAC /115VAC					
INPUT	VOLTAGE RANGE Note.4		85~264VAC (277VAC operational) 120~370VDC (390VDC operational)					
	FREQUENCY RANGE		47 ~ 63Hz					
	POWER FACTOR (Typ.)		PF>0.98/115VAC, PF>0.95/230VAC, PF>0.92/277VAC at full load					
	EFFICIENCY (Typ.)		90%	90%	92.5%	92.5%	93%	93.5%
	AC CURRENT (Typ.)	12V	2A / 115VAC 1.05A / 230VAC 0.9A/277VAC					
	AC CORRENT (Typ.)	15~54V	2.5A / 115VAC 1.3A / 230VAC 1.1A/277VAC					
	INRUSH CURRENT(Typ.)		COLD START 75A at 230VAC					
	LEAKAGE CURRENT		<0.75mA / 277VAC					
PROTECTION	OVER CURRENT		105 ~ 125%					
			Protection type: Constant current limiting, recovers automatically after fault condition is removed					
	SHORT CIRCUIT		Constant current limiting, recovers automatically after fault condition is removed					
	OVER VOLTAGE		13.5 ~ 18V	17.5 ~ 21.5V	27 ~ 34V	43 ~ 49V	55 ~ 63V	60 ~ 67V
			Protection type : SI	hut down and latch off	o/p voltage, re-power	on to recover		
	OVER TEMPERATURE		Shut down o/p voltage, recovers automatically after temperature goes down					
ENVIRONMENT	WORKING TEMP.		-55 ~ +70°C (Refer to "Derating Curve")					
	WORKING HUMIDITY		20 ~ 95% RH non-condensing					
	STORAGE TEMP., HUMIDITY		-60 ~ +80 °C, 10 ~ 95% RH non-condensing					
	TEMP. COEFFICIENT		±0.03%/℃ (0~60°C)					
	VIBRATION		20 ~ 500Hz, 10G 12min./1cycle, period for 72min. each along X, Y, Z axes					
SAFETY & EMC	SAFETY STANDARDS Note.8		UL62368-1, IEC62368-1, IP65 (or IP68 for HEP-240 Blank-Type), EAC TP TC 004 approved; Design refer to BS EN/EN62368-1					
	WITHSTAND VOLTAGE		I/P-O/P:3.75KVAC I/P-FG:2KVAC O/P-FG:1.5KVAC					
	ISOLATION RESISTANCE		I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH					
	EMC EMISSION		Compliance to BS EN/EN55032 (CISPR32) Class B, BS EN/EN61000-3-2,-3, EAC TP TC 020					
	EMC IMMUNITY		Compliance to BS EN/EN61000-4-2,3,4,5,6,8,11, BS EN/EN55024, light industry level (surge 6KV), criteria A, EAC TP TC 020					
OTHERS	MTBF		171.3K hrs min. MIL-HDBK-217F (25℃)					
	DIMENSION		244.2*68*38.8mm (L*W*H)					
	PACKING		1.3Kg; 12pcs/16.6Kg/0.84CUFT Ily mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature.					
NOTE	2. Ripple & noise are 3. Tolerance: include 4. Derating may be r 5. A-Type only. 6. Length of set up ti 7. The power supply complete installati 8. The water protecti 9. Refer to warranty 10. The ambient tem	e measure es set up needed ur me is me is conside on, the fin on level to statement perature of	Ad at 20MHz of band tolerance, line regulater low input voltage assured at cold first sered as a componer all equipment manufact for the IP68 rating of 3.5°C/10	dwidth by using a 12' ation and load regulates. Please check the start. Turning ON/OFF int that will be operate acturers must re-quate is performed 1000r 00m with fanless more discounting in the start.	twisted pair-wire termition. static characteristics the power supply m d in combination with lify EMC Directive on nm below the surface dels and of 5°C/1000i	ninated with a 0.1uf &	47uf parallel capacitors if the set up time. the EMC performance ion again. onth. operating altitude hig	will be affected by the






■ Mechanical Specification Case No.994H Unit:mm A-Type: HEP-240-_A(standard model) 244.2 220.2 300±20 FG (Green/Yellow) AC/L(Brown) AC/N(Blue) 300 ± 20 -V(Black) 110.1 34.2 89 (tc SJTW 18AWG×3C +V(Red) SJTW 14AWG×2C Vo ADJ. O ADJ. 34 ψ4.2×4PL • (tc): Max. Case Temperature

※ IP65 rated. Output voltage and constant current level can be adjusted through internal potentiometer. (Can access by removing the rubber stopper on the case.)

Blank-Type: HEP-240(optional model)



■ Installation Manual

Please refer to: http://www.meanwell.com/manual.html