

产品升级通知:LRS, RSP, HDR, KNX-20E 系列 OVC III 升级

明纬工业控制用电源供应器在全球市场上占有一席之地，为提升电源产品竞争力及扩大应用范围，针对 LRS-35/50/75/100/150/150F, RSP-75/100/150, HDR-15/30/60/100, KNX-20E 等系列产品应用需求之 Over Voltage Category(OVC) 安规参数进行提升，从 OVC II 至 OVC III (内容如下)。针对 OVC III 介绍，请参见明纬第 8 期电子报[电源供应器对于 Over Voltage Category\(OVC\) III 应用与要求](#)

本次修正不影响产品现有电气性能，明纬在安规及 EMC 报告上皆已完成报备，若您对本次产品变更有任何疑问，请与明纬业务代表联系。

升级前	<table border="1"> <tr> <td rowspan="5">ENVIRONMENT</td> <td>WORKING TEMP.</td> <td>-30 ~ +70°C (Refer to "Derating Curve")</td> </tr> <tr> <td>WORKING HUMIDITY</td> <td>20 ~ 90% RH non-condensing</td> </tr> <tr> <td>STORAGE TEMP., HUMIDITY</td> <td>-40 ~ +85°C, 10 ~ 95% RH</td> </tr> <tr> <td>TEMP. COEFFICIENT</td> <td>±0.03%/°C (0 ~ 50°C)</td> </tr> <tr> <td>VIBRATION</td> <td>10 ~ 500Hz, 5G 10min./1cycle, 60min. each along X, Y, Z axes</td> </tr> <tr> <td rowspan="5">SAFETY & EMC (Note 7)</td> <td>SAFETY STANDARDS</td> <td>UL60950-1, TUV EN60950-1, EN60335-1, EN61558-1/-2-16, CCC GB4943 approved</td> </tr> <tr> <td>WITHSTAND VOLTAGE</td> <td>I/P-O/P:3.75KVAC I/P-FG:2KVAC O/P-FG:1.25KVAC</td> </tr> <tr> <td>ISOLATION RESISTANCE</td> <td>I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH</td> </tr> <tr> <td>EMC EMISSION</td> <td>Compliance to EN55022 (CISPR22), GB9254 Class B, EN55014, EN61000-3-2Class A(≤75% Load), EN61000-3-3</td> </tr> <tr> <td>EMC IMMUNITY</td> <td>Compliance to EN61000-4-2,3,4,5,6,8,11, EN61000-6-2 (EN50082-2), heavy industry level, criteria A</td> </tr> </table>	ENVIRONMENT	WORKING TEMP.	-30 ~ +70°C (Refer to "Derating Curve")	WORKING HUMIDITY	20 ~ 90% RH non-condensing	STORAGE TEMP., HUMIDITY	-40 ~ +85°C, 10 ~ 95% RH	TEMP. COEFFICIENT	±0.03%/°C (0 ~ 50°C)	VIBRATION	10 ~ 500Hz, 5G 10min./1cycle, 60min. each along X, Y, Z axes	SAFETY & EMC (Note 7)	SAFETY STANDARDS	UL60950-1, TUV EN60950-1, EN60335-1, EN61558-1/-2-16, CCC GB4943 approved	WITHSTAND VOLTAGE	I/P-O/P:3.75KVAC I/P-FG:2KVAC O/P-FG:1.25KVAC	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH	EMC EMISSION	Compliance to EN55022 (CISPR22), GB9254 Class B, EN55014, EN61000-3-2Class A(≤75% Load), EN61000-3-3	EMC IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11, EN61000-6-2 (EN50082-2), heavy industry level, criteria A		
ENVIRONMENT	WORKING TEMP.		-30 ~ +70°C (Refer to "Derating Curve")																						
	WORKING HUMIDITY		20 ~ 90% RH non-condensing																						
	STORAGE TEMP., HUMIDITY		-40 ~ +85°C, 10 ~ 95% RH																						
	TEMP. COEFFICIENT		±0.03%/°C (0 ~ 50°C)																						
	VIBRATION	10 ~ 500Hz, 5G 10min./1cycle, 60min. each along X, Y, Z axes																							
SAFETY & EMC (Note 7)	SAFETY STANDARDS	UL60950-1, TUV EN60950-1, EN60335-1, EN61558-1/-2-16, CCC GB4943 approved																							
	WITHSTAND VOLTAGE	I/P-O/P:3.75KVAC I/P-FG:2KVAC O/P-FG:1.25KVAC																							
	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH																							
	EMC EMISSION	Compliance to EN55022 (CISPR22), GB9254 Class B, EN55014, EN61000-3-2Class A(≤75% Load), EN61000-3-3																							
	EMC IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11, EN61000-6-2 (EN50082-2), heavy industry level, criteria A																							
升级后	<table border="1"> <tr> <td rowspan="5">ENVIRONMENT</td> <td>WORKING TEMP.</td> <td>-30 ~ +70°C (Refer to "Derating Curve")</td> </tr> <tr> <td>WORKING HUMIDITY</td> <td>20 ~ 90% RH non-condensing</td> </tr> <tr> <td>STORAGE TEMP., HUMIDITY</td> <td>-40 ~ +85°C, 10 ~ 95% RH non-condensing</td> </tr> <tr> <td>TEMP. COEFFICIENT</td> <td>±0.03%/°C (0 ~ 50°C)</td> </tr> <tr> <td>VIBRATION</td> <td>10 ~ 500Hz, 5G 10min./1cycle, 60min. each along X, Y, Z axes</td> </tr> <tr> <td rowspan="5">SAFETY & EMC (Note 7)</td> <td>OVER VOLTAGE CATEGORY</td> <td>III : Compliance to EN61558, EN50178, EN60664-1, EN62477-1; altitude up to 2000 meters</td> </tr> <tr> <td>SAFETY STANDARDS</td> <td>UL60950-1, TUV EN60950-1, EN60335-1, EN61558-1/-2-16, CCC GB4943.1, BSMI CNS14336-1, EAC TP TC 004, AS/NZS 60950.1 (by CB) approved</td> </tr> <tr> <td>WITHSTAND VOLTAGE</td> <td>I/P-O/P:4KVAC I/P-FG:2KVAC O/P-FG:1.25KVAC</td> </tr> <tr> <td>ISOLATION RESISTANCE</td> <td>I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH</td> </tr> <tr> <td>EMC EMISSION</td> <td>Compliance to EN55032 (CISPR32) Class B, EN55014, EN61000-3-2,-3, GB/T 9254, BSMI CNS13438, EAC TP TC 020</td> </tr> <tr> <td>EMC IMMUNITY</td> <td>Compliance to EN61000-4-2,3,4,5,6,8,11, EN61000-6-2 (EN50082-2), heavy industry level, criteria A, EAC TP TC 020</td> </tr> </table>	ENVIRONMENT	WORKING TEMP.	-30 ~ +70°C (Refer to "Derating Curve")	WORKING HUMIDITY	20 ~ 90% RH non-condensing	STORAGE TEMP., HUMIDITY	-40 ~ +85°C, 10 ~ 95% RH non-condensing	TEMP. COEFFICIENT	±0.03%/°C (0 ~ 50°C)	VIBRATION	10 ~ 500Hz, 5G 10min./1cycle, 60min. each along X, Y, Z axes	SAFETY & EMC (Note 7)	OVER VOLTAGE CATEGORY	III : Compliance to EN61558, EN50178, EN60664-1, EN62477-1; altitude up to 2000 meters	SAFETY STANDARDS	UL60950-1, TUV EN60950-1, EN60335-1, EN61558-1/-2-16, CCC GB4943.1, BSMI CNS14336-1, EAC TP TC 004, AS/NZS 60950.1 (by CB) approved	WITHSTAND VOLTAGE	I/P-O/P:4KVAC I/P-FG:2KVAC O/P-FG:1.25KVAC	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH	EMC EMISSION	Compliance to EN55032 (CISPR32) Class B, EN55014, EN61000-3-2,-3, GB/T 9254, BSMI CNS13438, EAC TP TC 020	EMC IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11, EN61000-6-2 (EN50082-2), heavy industry level, criteria A, EAC TP TC 020
ENVIRONMENT	WORKING TEMP.		-30 ~ +70°C (Refer to "Derating Curve")																						
	WORKING HUMIDITY		20 ~ 90% RH non-condensing																						
	STORAGE TEMP., HUMIDITY		-40 ~ +85°C, 10 ~ 95% RH non-condensing																						
	TEMP. COEFFICIENT		±0.03%/°C (0 ~ 50°C)																						
	VIBRATION	10 ~ 500Hz, 5G 10min./1cycle, 60min. each along X, Y, Z axes																							
SAFETY & EMC (Note 7)	OVER VOLTAGE CATEGORY	III : Compliance to EN61558, EN50178, EN60664-1, EN62477-1; altitude up to 2000 meters																							
	SAFETY STANDARDS	UL60950-1, TUV EN60950-1, EN60335-1, EN61558-1/-2-16, CCC GB4943.1, BSMI CNS14336-1, EAC TP TC 004, AS/NZS 60950.1 (by CB) approved																							
	WITHSTAND VOLTAGE	I/P-O/P:4KVAC I/P-FG:2KVAC O/P-FG:1.25KVAC																							
	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH																							
	EMC EMISSION	Compliance to EN55032 (CISPR32) Class B, EN55014, EN61000-3-2,-3, GB/T 9254, BSMI CNS13438, EAC TP TC 020																							
EMC IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11, EN61000-6-2 (EN50082-2), heavy industry level, criteria A, EAC TP TC 020																								

明纬企业股份有限公司

企划部